

Globe Valve Solutions Made Simple.



Belimo New Generation Globe Valve Actuators and Retrofit Linkages Offer Greater Power and Flexibility.

No two applications are exactly alike; new or old, they all vary in their demands. Whether it's high pressure steam or difficult installations, New Generation Globe Valve Actuators are designed to adapt to these challenges offering easy installation and field adjustability. They can be adapted to most globe valves, regardless of make.

The New Generation Globe Valve Actuators incorporate not only strength, but flexibility too. Engineered to suit a broad range of HVAC applications, the new actuators and retrofit linkages are highly adaptable making selection, installation and service hassle-free.

- Travel ranges of up to 2" (50mm) on EV and RV series.
- Multiple voltage options (24V and 120-230V).
- Universal linkages can retrofit most globe valves, regardless of make.
- Increased force ranges for higher close-off pressures.
- Field selectable fail-safe position switches.
- Lower power consumption during operation.
- Easy selection process, minimized inventory.



True Flexibility.

LED Button

Adapts to stroke of the valve.

Fail-Safe Switch ("K" models only)

Selectable position to drive stem up or stem down.

Coupler

Locking feature to prevent slipping. Doubles as position indicator.

Cast Aluminum Linkage


Rugged design with zero deflection.

MFT Interface Plug

Access MFT capabilities and programming.

Manual Override

Ability to drive the valve up or down during power failure.



As a leading manufacturer of electronic direct-coupled actuators and motorized valves, Belimo is committed to help improve comfort, safety and efficiency in buildings. Our new generation actuators and retrofit linkages provide increased force and constant speed to withstand high-pressure applications. The linear stroke operation ensures that consistent ambient temperatures are maintained in heating and cooling systems.

More Strength for Higher Pressure Demands

The New Generation Globe Valve Actuator has the "extra muscle" needed for applications where higher close-off pressures are required. Available on globe valves or with a retrofit linkage, these new actuators offer greater force up to 1011 lbf. The actuators are designed to withstand the rigorous demands of many HVAC applications.

With its innovative valve clamp and quick connect coupler, the New Generation Globe Valve Actuator can be installed and adapted in minutes.

Selection Made Easy.

Globe Valve Body		Size	Suitable Actuators		Actuator Specifications
2-Way NPT	3-Way NPT	Inches	Non-Spring Return	Electronic Fail-Safe	
G212, G212S		1/2"	LV Series 112 lbf [500 N]	LVK Series 112 lbf [500 N]	Control Type On/Off, Floating Point, PWM, Proportional, 2-10 VDC, Multi-Function Technology (MFT) Manual Override Non-Spring Return Electronic Fail-Safe Running Time 90 seconds (default) 60-150 seconds variable Actuator Travel Range [mm] 0.6" [15] LV, 0.75" [20] SV, 1.25" [32] AV, 2" [50] EV and RV
G213, G213S		1/2"			
G214, G214S	G314	1/2"			
G215, G215S	G315, G315D	1/2"			
G219, G219S		3/4"			
G220, G220S	G320, G320D	3/4"			
G224, G224S		1"	SV Series 337 lbf [1500 N]	SVK Series 337 lbf [1500 N]	
G225, G225S	G325, G325D	1"			
G232, G232S	G332, G332D	1 1/4"			
G240, G240S	G340, G340D	1 1/2"			
G250, G250S	G350, G350D	2"			

Globe Valve Body	Size	Suitable Actuators	
2-Way Flanged	Inches	Non-Spring Return	Electronic Fail-Safe
G665C, G665CS, G665LCS, G665C-250, G665CS-2250	2 1/2"	EV Series 562 lbf [2500 N]	AVK 450 lbf [2000 N]
G680C, G680CS, G680LCS, G680C-250, G680CS-2250	3"		
G6100C, G6100CS, G6100LCS, G6100C-250, G6100CS-2250	4"		
G6125C, G6125CS, G6125LCS, G6125C-250, G6125CS-2250	5"		
G6150C, G6150CS, G6150LCS, G6150C-250, G6150CS-2250	6"		

Globe Valve Body	Size	Suitable Actuators		
3-Way Flanged	Inches	Non-Spring Return		Electronic Fail-Safe
G765, G765 S, G765-250, G765 S-250	2 1/2"	EV	RV Series 1011 lbf [4500 N]	AVK
G780, G780 S, G780-250, G780 S-250	3"			
G7100, G7100 S, G7100-250, G7100 S-250	4"			
G7125, G7125 S, G7125-250, G7125 S-250	5"			
G7150, G7150 S, G7150-250, G7150 S-250	6"			
G765D, G765DS, G765DS-250	2 1/2"	EV Series 562 lbf [2500 N]		AVK Series 450 lbf [2000 N]
G780D, G780DS, G780DS-250	3"			
G7100D, G7100DS, G7100DS-250	4"			
G7125D, G7125DS, G7125DS-250	5"			
G7150D, G7150DS, G7150DS-250	6"			



New Universal Globe Valve Linkages Incorporate Strength and Flexibility.



Product Range

Linkage	Valve Body Model	Valve Manufacturer	Suitable Actuators									
			Non-Spring Return		Electronic Fail-Safe							
SGVL ½" - 2"	VB7000, VB9000 Series	Schneider Siebe Invensys Barber Colman	LV Series 112 lbf [500 N]	SV Series 337 lbf [1500 N]		LVK Series 112 lbf [500 N]	SVK Series 337 lbf [1500 N]					
	G2, G2...S, G3 Series	Belimo										
UGVL ½" - 2"	V(B)-3754, V(B)-3974, V(B)-4324, V(B)-5844, V-4332, VG7000 Series	Johnson Controls										
	V6600, V6700, V6800	Robertshaw										
	V5011, V5011N, V5013, V5013N Series	Honeywell										
	591, 599, 658 Series	Siemens Landis Powers										
WGVL 2½" - 6"	Type 20, Type 22, Type 30, Type 32	Warren Controls								EV 562 lbf [2500 N]	RV 1011 lbf [4500 N]	AVK 450 lbf [2000 N]
New FGVL 2½" - 6"	V3..., V4..., V5..., VG2..., VG82... V5..., V33..., V34... 591, 599 VB9..., VB304..., VB804...	Johnson Controls Honeywell Siemens Siebe/BC/Invensys										

A versatile product for many HVAC applications.

- Easy installation.
- Adjustable UGVL linkage to fit on most ½" to 2" globe valves.
- Full range of electronic fail-safe and non-spring return options.
- Increased force ranges for higher close off pressures.
- Steam inlet ranges up to 100 psi.
- Customized ordering, i.e. cable length, run times, etc.
- Adjustable FGVL linkage to fit on most 2½" to 6" globe valves.



RETROFIT

Belimo worldwide: www.belimo.com

BELIMO Americas

USA Locations, 43 Old Ridgebury Road, Danbury, CT 06810
Tel. 800-543-9038, Fax 800-228-8283, marketing@us.belimo.com

1049 Fortunato Loop, Sparks, NV 89436
Tel. 800-987-9042, Fax 800-987-8875, marketing@us.belimo.com

Canada Locations, 5845 Kennedy Road, Mississauga, Ontario L4Z 2G3
Tel. 866-805-7089, Fax 905-712-3124, marketing@us.belimo.com

Latin America and the Caribbean Customer Service
Tel. 203-791-8396, Fax 203-791-9139, marketing@us.belimo.com

Belimo Brasil Comércio de Automação Ltda.
Tel: 55 11 3643-5656, Fax: 55 11 3643 5657, atendimentoaocliente@br.belimo.com.

